



Product Specification Sheet

VWR PIPETTE TIPS RACKED STERILE

VWR International certifies that the specified products meet all VWR specifications and quality criteria for release. The products comply in every respect with the relevant particular specifications, drawings, relevant standards and regulations in force.

VWR International certifie que les produits mentionnés respectent toutes les spécifications et critères de qualité VWR. Les produits satisfont aux spécifications particulières, aux plans, aux normes et règlements en vigueur s'y rapportant.

VWR International bestätigt hiermit, daß die angegebenen Produkte alle VWR Spezifikationen und Qualitätskriterien zur Freigabe erfüllen. Die Produkte entsprechen in jeder Hinsicht den maßgeblichen Spezifikationen, den Zeichnungen sowie den relevanten Normen und gültigen Vorschriften.

Material: **Polypropylene**

Cat. No.	Type	Capacity (µl)	Compatibility	Packed	Pk
732-0516	UltraFine™, graduated	0.1 - 10	AF1	12 racks, 96 each	1.152
732-0543	UltraFine™, extended	0.1 - 10	AF1	10 racks, 96 each	960
732-0519	Bevel Point™, graduated	0.5 - 10	AF2	10 racks, 96 each	960
732-1101	UltraFine™, graduated	0.5 - 10	AF16	10 racks, 96 each	960
732-0799	HighRecovery™	0.1 - 20	AF13	10 racks, 96 each	960
732-1100	Micro	0.1 - 30	AF1	10 racks, 96 each	960
732-0525	Bevel Point™ (5×192)	1 - 40	AF3	5 racks, 192 each	960
732-0528	Bevel Point™ (10×96)	1 - 40	AF3	10 racks, 96 each	960
732-0520	Bevel Point™	1 - 50	AF4	10 racks, 96 each	960
732-1105	UltraFine™, FlexTop™, graduated	1 - 50	AF4	10 racks, 96 each	960
732-1102	Bevel Point™, graduated	1 - 100	AF5	10 racks, 96 each	960
732-1103	Standard	1 - 100	AF5	10 racks, 96 each	960
732-1107	UltraFine™, extended	1 - 100	AF5	6 racks, 96 each	576
732-0523	Bevel Point™	1 - 100	AF5	10 racks, 96 each	960
732-0530	Bevel Point™ (10×96)	1 - 160	AF6	10 racks, 96 each	960
732-0573	Bevel Point™ (5×192)	1 - 160	AF6	5 racks, 192 each	960
732-0800	HighRecovery™	1 - 200	AF13	10 racks, 96 each	960
732-0541	UltraFine™	1 - 200	AF7	10 racks, 96 each	960
732-0544	Bevel Point™, wide orifice	1 - 200	AF7	10 racks, 96 each	960

VWR International bvba/sprl, Researchpark Haasrode 2020, Geldenaaksebaan 464, 3001 Leuven, Belgium

<http://www.vwr.com>



Version: 2.0



Product Specification Sheet

Cat. No.	Type	Capacity (µl)	Compatibility	Packed	Pk
732-0610	UltraFine™, extended	1 - 200	AF7	6 racks , 96 each	576
732-0611	UltraFine™, extended	1 - 300	AF8	6 racks , 96 each	576
732-0537	Bevel Point™	1 - 300	AF8	10 racks, 96 each	960
732-0801	HighRecovery™	100 - 1000	AF13	6 racks, 96 each	576
732-0534	UltraFine™	100 - 1000	AF9	6 racks , 96 each	576
732-1106	UltraFine™, FlexTop™	100 - 1000	AF9	6 racks, 96 each	576

Other Characteristics:

- All the tips are made of high quality 100% pure virgin medical grade PP.
- Made in the highest quality moulds, these tips can be used whenever the work demands a higher standard.
- Resins are pre-tested for metal contamination.
- A wider seal assures that tips will seal easily and consistently without leaking on old as well as new pipettes

Pyrogens:

Certified testing is performed lot by lot. These tests include Nuclease (Rnase,Dnase) and Endotoxin (pyrogen). Certificates are on file at the production facility.

Sterility Testing:

Those products designated as Sterile are irradiated by gamma radiation. The validated dosage level for these products is in a range between 12-25kGy.

Disclaimer: VWR wants to state that these specifications can only be regarded as general information and will not discharge the user from his obligation to ensure the product is suitable for the intended use - If there is any doubt ask us.

Date of issue: **April 2013**

VWR International bvba/sprl, Researchpark Haasrode 2020, Geldenaaksebaan 464, 3001 Leuven, Belgium

<http://www.vwr.com>



Version: 2.0